

Patch-Cord

compatible with UC^{CONNECT} system

Specification

Product Family	Related Cable Description
UC ^{CONNECT} 300 Class D Channel, unshielded	Cat.5e U/UTP 26/7 AWG 4P patch cable LSHF
UC ^{CONNECT} 400 Class E Channel, unshielded	Cat.6 U/UTP 26/7 AWG 4P patch cable LSHF

Performance

Item	Description
Flame resistance - PVC	IEC 60332-1
Flame resistance - LSHF	IEC 60332-1, IEC 60754-2, IEC 61034
Standards	EN 50173, ISO/IEC 11801 Amendment 2, IEC 60603-7
Length	2m, 3m, other lengths upon request



Flexible cables with RJ45 connectors

- Flexible stranded bare copper conductor patch cable
- 2xRJ45 connector (TIA568-B coding)
- Proven performance

Technical data

Product code	Product name	Measures	Weight	Items per packaging unit
		Length in cm	g	Packaging option
YPCBP00134 YPCBP00135 YPCBP00136 YPCBP00137	UC C300 PC UU GY L 00100 UC C300 PC UU GY L 00200 UC C300 PC UU GY L 00300 UC C300 PC UU GY L 00500	LLLLL: Length option; length in cm (example: 00200 -> 2,0m)	n/a	1 = 1 per bag, 2 = 5 per bag, 3 = 10 per bag)
YPCBP00155 YPCBP00156 YPCBP00157 YPCBP00158	UC C400 PC UU GY L 00100 UC C400 PC UU GY L 00200 UC C400 PC UU GY L 00300 UC C400 PC UU GY L 00500	LLLLL: Length option; length in cm (example: 00200 -> 2,0m)	n/a	1 = 1 per bag, 2 = 5 per bag, 3 = 10 per bag)

CM – length in centimeters • Standard colours acc. to table • Packaging option to be identified with order information

2.5. Patch Leads