

## 5.4. System Patch-Cords



- UC<sup>Connect</sup> System Patch-Cords
- Flexible stranded bare copper conductor patch cable
- 3p Component Compliant
- 2xRJ45 connector (TIA568-B coding)
- Different jacketing options
- Different colour options (grey, blue, aqua, yellow, orange, red, green, black)
- DualBoot molded strain relief
- Latch protector

# Draka UC<sup>Connect</sup> Patch-Cords

## Category 6a DualBoot U/UTP 24AWG 500MHz

### Specification

Product Family	Related Cable Description
UC <sup>Connect</sup> 500 Class Ea Channel, Unshielded	Cat.6a U/UTP 24 AWG 4P patch cable LSHF

### Performance

Item	Description
Flame resistance - PVC	IEC 60332-1
Flame resistance - LSHF	IEC 60332-1, IEC 60754-2, IEC 61034
Standards	EN 50173, ISO/IEC 11801 Amendment 2, IEC 60603-7
Length	1m, 2m, 3m, & 5m other lengths upon request

### Technical data

Product code	Product name	Description	Weight	Items per packaging unit
			g	
YPCBP01692	UC C500 PC UU GY 00100	U/UTP Cat.6a DBOOT Patch cord LSZH 24AWG 1M Grey	31.7	1
YPCBP01693	UC C500 PC UU GY 00150	U/UTP Cat.6a DBOOT Patch cord LSZH 24AWG 1.5M Grey	47.55	1
YPCBP01694	UC C500 PC UU GY 00200	U/UTP Cat.6a DBOOT Patch cord LSZH 24AWG 2M Grey	63.4	1
YPCBP01695	UC C500 PC UU GY 00300	U/UTP Cat.6a DBOOT Patch cord LSZH 24AWG 3M Grey	95.1	
YPCBP01696	UC C500 PC UU GY 00400	U/UTP Cat.6a DBOOT Patch cord LSZH 24AWG 4M Grey	126.8	1
YPCBP01697	UC C500 PC UU GY 00500	U/UTP Cat.6a DBOOT Patch cord LSZH 24AWG 5M Grey	158.5	1
YPCBP01698	UC C500 PC UU GY 00700	U/UTP Cat.6a DBOOT Patch cord LSZH 24AWG 7M Grey	221.9	1
YPCBP01699	UC C500 PC UU GY 01000	U/UTP Cat.6a DBOOT Patch cord LSZH 24AWG 10M Grey	317	1
YPCBP01700	UC C500 PC UU GY 01500	U/UTP Cat.6a DBOOT Patch cord LSZH 24AWG 15M Grey	475.5	1
YPCBP01701	UC C500 PC UU GY 02000	U/UTP Cat.6a DBOOT Patch cord LSZH 24AWG 20M Grey	634	1