

# UC<sup>CONNECT</sup> Patchcord 4P

Cat8.2 – Cat8.2, 1/10GbE Ethernet, colour yellow/grey  
Side A: Cat8.2-plug, 4 pair, Side B: Cat8.2-plug, 4 pair

## 6.4. Patch Leads

### Specification

Item	Description
<b>Cable</b>	4P 4x2xAWG26/7 S/FTP, flex., 100 Ohm Outer jacket: Compound free of halogens
<b>A Side</b>	Cat8.2 plug 4P bend relief yellow
<b>B Side</b>	Cat8.2 plug 4P bend relief yellow
<b>Colours</b>	Grey RAL7035 or yellow RAL1021



- Patch Cord 4-Pair, Category 8.2 – Category 8.2
- 4 Chamber Design
- Fully compatible with Cat 7 and Cat 7a
- Shielded Design
- 3rd Party Approved by GHMT
- 1 / 10GbE

### Technical data

Product code	Product name	Description	Weight	Items per packaging unit
			g	
<b>YPCBP01886</b>	UC C2000 PC 4P 4P SF GY L00050	Patchcord 4P Cat8.2 - RJ45, 1 GbE / 10 GbE Ethernet, colour yellow/grey, Side A: Cat8.2-plug, 4 pair , Side B: Cat8.2-plug, 4 pair, length 0,50 m	34	10
<b>YPCBP01887</b>	UC C2000 PC 4P 4P SF GY L00100	Patchcord 4P Cat8.2 - RJ45, 1 GbE / 10 GbE Ethernet, colour yellow/grey, Side A: Cat8.2-plug, 4 pair, Side B: Cat8.2-plug, 4 pair, length 1,0 m	50	10
<b>YPCBP01888</b>	UC C2000 PC 4P 4P SF GY L00150	Patchcord 4P Cat8.2 - RJ45, 1 GbE / 10 GbE Ethernet, colour yellow/grey, Side A: Cat8.2-plug, 4 pair Side B: Cat8.2-plug, 4 pair, length 1,50 m	69	10
<b>YPCBP01889</b>	UC C2000 PC 4P 4P SF GY L00200	Patchcord 4P Cat8.2 - RJ45, 1 GbE / 10 GbE Ethernet, colour yellow/grey, Side A: Cat8.2-plug, 4 pair , Side B: Cat8.2-plug, 4 pair, length 2,0 m	72	10
<b>YPCBP01890</b>	UC C2000 PC 4P 4P SF GY L00300	Patchcord 4P Cat8.2 - RJ45, 1 GbE / 10 GbE Ethernet, colour yellow/grey, Side A: Cat8.2-plug, 4 pair , Side B: Cat8.2-plug, 4 pair, length 3,0 m	97	10
<b>YPCBP01891</b>	UC C2000 PC 4P 4P SF GY L00500	Patchcord 4P Cat8.2 - RJ45, 1 GbE / 10 GbE Ethernet, colour yellow/grey, Side A: Cat8.2-plug, 4 pair, Side B: Cat8.2-plug, 4 pair, length 5,0 m	120	10