

6.4. Patch Leads



- Patch Cord 4-Pair, Category 8.2 – Category 8.2
- 4 Chamber Design
- Fully compatible with Category 7 and Category 7a
- Shielded Design
- 3rd Party Approved by GHMT
- 40GbE

UC^{CONNECT} Patchcord 4P

Cat8.2 – Cat8.2, 1/40GbE Ethernet, colour grey/grey
Side A: Cat8.2-plug, 4 pair, Side B: Cat8.2-plug, 4 pair

Specification

Item	Description
Cable	4P 4x2xAWG26/7 S/FTP, flex., 100 Ohm Outer jacket: Compound free of halogens
A Side	Cat8.2 plug 4P bend relief yellow
B Side	Cat8.2 plug 4P bend relief yellow
Colours	Grey RAL7035 or yellow RAL1021

Technical data

Product code	Product name	Description	Weight	Items per packaging unit
			g	
YPCBP02495	UC C2000 PC 4P 4P SF GYL00050 40GbE	Patchcord 4P Cat8.2 - 4P Cat8.2, 40 GbE Ethernet 8.2 flex, color grey/grey Side A: Cat8.2 Plug, 4 pair Side B: Cat8.2 Plug, 4 pair length 0.50 m	34	10
YPCBP02496	UC C2000 PC 4P 4P SF GY L00100 40GbE	Patchcord 4P Cat8.2 - 4P Cat8.2, 40 GbE Ethernet 8.2 flex, color grey/grey Side A: Cat8.2 Plug, 4 pair Side B: Cat8.2 Plug, 4 pair length 1.00 m	50	10
YPCBP02497	UC C2000 PC 4P 4P SF GY L00100 40GbE	Patchcord 4P Cat8.2 - 4P Cat8.2, 40 GbE Ethernet 8.2 flex, color grey/grey Side A: Cat8.2-plug, 4 pair Side B: Cat8.2-plug, 4 pair length 1.50 m	69	10
YPCBP02498	UC C2000 PC 4P 4P SF GY L00200 40GbE	Patchcord 4P Cat8.2 - 4P Cat8.2, 40 GbE Ethernet 8.2 flex, color grey/grey Side A: Cat8.2 Plug, 4 pair Side B: Cat8.2 Plug, 4 pair length 2.00 m	72	10
YPCBP02499	UC C2000 PC 4P 4P SF GY L00500 40GbE	Patchcord 4P Cat8.2 - 4P Cat8.2, 40 GbE Ethernet 8.2 flex, color grey/grey Side A: Cat8.2-plug, 4 pair Side B: Cat8.2-plug, 4 pair length 5.00 m	120	10