

Patch-Cord

compatible with UC^{CONNECT} system



4.3. Patch Leads

Specification

Product Family	Related Cable Description
UC ^{CONNECT} 500 Class Ea Channel, screened	Cat.7 S/FTP 26/1 AWG 4P cable LSHF especially for CP application

Performance

Item	Description
Flame resistance - PVC	IEC 60332-1
Flame resistance - LSHF	IEC 60332-1, IEC 60754-2, IEC 61034
Standards	EN 50173, ISO/IEC 11801 Amendment 2, IEC 60603-7
Length	2m, 3m, other lengths upon request



Flexible cables with RJ45 connectors for specific channel performance

- Flexible stranded bare copper conductor patch cable
- Flexible solid bar copper conductor CP cable
- 2xRJ45 connector (TIA568-B coding)
- Proven performance
- Different jacketing options
- Different colour options (grey, blue, aqua, yellow, orange, red, green, black)
- DualBoot molded strain relief
- Latch protector

Technical data

Product code	Product name	Measures	Weight	Items per packaging unit
		Length in cm	g	Packaging option
YPCBP00170	UC C500 PC SF GY L 00100	LLLLL: Length option; length in cm (example: 00200 -> 2,0m)	n/a	1 = 1 per bag, 2 = 5 per bag, 3 = 10 per bag)
YPCBP00171	UC C500 PC SF GY L 00200			
YPCBP00172	UC C500 PC SF GY L 00300			
YPCBP00173	UC C500 PC SF GY L 00500			

CM – length in centimeters • Standard colours acc. to table • Packaging option to be identified with order information

Related Products				
YMCBP00183	UC CACC PC Marking Clip blue 50pc		n/a	50 pieces
YMCBP00184	UC CACC PC Marking Clip yellow 50pc		n/a	50 pieces
YMCBP00185	UC CACC PC Marking Clip green 50pc		n/a	50 pieces
YMCBP00186	UC CACC PC Marking Clip black 50pc		n/a	50 pieces
YMCBP00187	UC CACC PC Marking Clip red 50pc		n/a	50 pieces