

# UC COMF PP SD HT BK

## 1U PSP splice and patch shelf

### Construction

<b>Max. Cable Diameter (mm):</b>	18
<b>Cable capacity</b>	2
<b>Required space envelope (mm)</b>	(w) 481 x (d) 230 x (h) 44
<b>Operating temperature:</b>	-20oC to + 50oC (5 to 95% RH)
<b>Material</b>	High Impact Polystyrene (Fire Retardant)
<b>Colour</b>	Light Grey RAL 7035
<b>Testing:</b>	
<b>Optical</b>	Tested at 1310nm and 1550nm
<b>Dry heat</b>	BS EN 60068-2-2 Test Bb
<b>Change of temperature</b>	IEC 68-2-14
<b>Vibration</b>	IEC 68-2-6
<b>Shock</b>	IEC 68-2-27



- Standard range of high density, low cost, compact designs for up to 24 fibres using SC or ST connectors.
- Standard range of high density, low cost, compact designs for up to 48 fibres using SC or LC connectors.
- Compatible with Prysmian Sirocco Blown Fibre Tube Cables using a Blown Fibre Manifold. The manifold enables up to 6 blown fibre tubes to be routed to a single shelf.

### Technical data

Item No.	SAP Description	Material Description	Weight	Items per packaging unit
			kg	
<b>YPPBP01515</b>	UC COMF PP SD HT BK 12 1U	12 Port, SC Duplex Multimode Adaptors Only	1.1	1
<b>YPPBP01516</b>	UC COMF PP SD HT BK 24 1U	24 Port, SC Duplex Multimode Adaptors Only	1.1	1
<b>YPPBP01517</b>	UC COMF PP SD HT BK 48 1U	48 Port, SC Duplex Multimode Adaptors Only	1.1	1
<b>YPPBP01518</b>	UC COMF PP LD HT BK 12 1U	12 Port, LC Duplex Multimode Adaptors Only	1.1	1
<b>YPPBP01519</b>	UC COMF PP LD HT BK 24 1U	24 Port, LC Duplex Multimode Adaptors Only	1.1	1
<b>YPPBP01520</b>	UC COMF PP LD HT BK 48 1U	48 Port, LC Duplex Multimode Adaptors Only	1.1	1
<b>YPPBP01521</b>	UC COMF PP ST HT BK 12 1U	12 Port, ST Simplex Multimode Adaptors Only	1.1	1
<b>YPPBP01522</b>	UC COMF PP ST HT BK 24 1U	24 Port, ST Simplex Multimode Adaptors Only	1.1	1
<b>YPPBP01523</b>	UC COSF PP SD HT BK 12 1U	12 Port, SC Duplex Singlemode Adaptors Only	1.1	1
<b>YPPBP01524</b>	UC COSF PP SD HT BK 24 1U	24 Port, SC Duplex Singlemode Adaptors Only	1.1	1
<b>YPPBP01525</b>	UC COSF PP SD HT BK 48 1U	48 Port, SC Duplex Singlemode Adaptors Only	1.1	1
<b>YPPBP01526</b>	UC COSF PP LD HT BK 12 1U	12 Port, LC Duplex Singlemode Adaptors Only	1.1	1
<b>YPPBP01527</b>	UC COSF PP LD HT BK 24 1U	24 Port, LC Duplex Singlemode Adaptors Only	1.1	1
<b>YPPBP01528</b>	UC COSF PP LD HT BK 48 1U	48 Port, LC Duplex Singlemode Adaptors Only	1.1	1