

## MK2 Ultra Compact Termination Box

**Prysmian Part Number: See Table Below**



The MK2 Ultra Compact Termination Box is designed for use in residential and business applications for the termination of up to two fibres. The wall box enables the installation of a small cable to be spliced to up to two SC pigtails (PC or APC), which connect to shuttered adapters at the base of the unit. The unit can be quickly installed within an office, house or communication room environment.

### Features and Benefits

- Compact and attractive design for internal use.
- Ability to allow cables to enter from rear, bottom, top or either side of the unit.
- All fibres are positively managed to maintain a 20mm minimum bend radius.
- Supplied with pre-installed fibre pigtails.
- Flip tray to allow access to connectorised tails and cable entry.
- Removable cover for easy access. Cover has a transparent label cover for identification.
- Supplied with a security screw to prevent unauthorised access.
- Unit manufactured from fire resistant UL94-V0 rated material.
- Patchcords exit unit on bottom face via two shuttered SC adapters.
- Standard colour white RAL 9016. Other colours available on request.
- Ability to accommodate field mounted connectors (Please contact Prysmian to discuss your requirements).

### Kit Contents

The MK2 Ultra Compact Termination Box is supplied with wall fixings, a security screw, a label cover and cable ties. Pigtails and adaptors can be pre-installed or sold separately. See Part numbers opposite.

### Additional Items

- Splice Protectors.

### Optional Items

(if required as separate items)

- Patch Chords (refer to data sheet AC004).
- Adapters.
- Pigtails.

### Part Numbers

Supplied With	Part Number
1 SC/UPC adaptor (no pigtail)	<a href="#">XCPSC01036</a>
1 SC/APC adaptor (no pigtail)	<a href="#">XCPSC01041</a>
2 SC/UPC adaptors (no pigtails)	<a href="#">XCPSC01037</a>
2 SC/APC adaptors (no pigtails)	<a href="#">XCPSC01042</a>
1 SC/UPC pigtail and adaptor	<a href="#">XCPSC00607</a>
1 SC/APC pigtail and adaptor	<a href="#">XCPSC00608</a>
2 SC/UPC pigtails and adaptors	<a href="#">XCPSC00609</a>
2 SC/APC pigtails and adaptors	<a href="#">XCPSC00610</a>

## Technical Data

- Number of input cable positions: 7
- Max input cable diameter (mm): 6mm
- Maximum Capacity: 2 Fibres
- Maximum no. of customer feeds: 2 Patchcords
- Required space envelope (mm): (l) 106 x (w) 83.5 x (d) 25
- Operating temperature: -40°C to + 70°C (5 to 95% RH)
- Material:-
  - Base: FR ABS, White RAL 9016
  - Cover: FR ABS, White RAL 9016
  - Splice tray: FR ABS, White RAL 9016
- Testing:-
  - Optical: Tested 1310,1550 & 1625nm
  - Transportation: FT/RD/RESA/09/11/213 – 3.3
  - Installation: FT/RD/RESA/09/11/213 – 3.4
  - Climatic Storage: FT/RD/RESA/09/11/213 – 3.8
  - Impact: FT/RD/RESA/09/11/213 – 3.8
  - Cover Resistance: FT/RD/RESA/09/11/213 – 3.10
  - Tensile: FT/RD/RESA/09/11/213 – 3.12
  - Torsion: FT/RD/RESA/09/11/213 – 3.13
  - Insertion Loss: FT/RD/RESA/09/11/213 – 3.14
  - Climatic Testing: FT/RD/RESA/09/11/213 – 3.15

## Logistics

- Packing Dimensions (mm): (l) 115  
(w) 95  
(d) 35
- Packed Weight (kg): 0.080
- Net weight (kg): 0.073

## Pigtail Technical Data

Pigtails are supplied with either xx/UPC or xx/APC connectors.

xx/UPC connectors can be used in cases where xx/PC or xx/SPC connectors are required.

For technical data on the pigtails supplied refer to Prysmian data sheet AC003

## Additional Items

### Heatshrink Splice Protectors

Heatshrink Splice Protectors are used to protect the fibre splice. They are 2.4mm in diameter and 45mm in length.

- Prysmian Part No. - XPESC00031 (pack of 50)**  
**- XPESC00056 (pack of 12)**



### Mechanical Splices

Mechanical Splices are used to splice fibres together without the need of a fusion splicing machine. They are 4mm wide x 4mm tall and 40mm in length. An assembly tool and splice holder is required for installation. See Prysmian data sheet AC007 for further information on mechanical splices.

- Prysmian Part No. - XKTSC00121 (pack of 50)**




## Additional Items continued

### Crimp Splice Protectors

Crimp Splice Protectors are used to protect the fibre splice. They are 1.2mm wide x 3.2mm high x 30mm long. Crimp Splice Protector Holders are required in order to accommodate crimp splices in the termination box. See below.


**Prysmian Part No. – XKTSC00079 (pack of 12)**  
**XKTSC00078 (pack of 50)**



### Crimp Splice Protector Holders

Crimp Splice Protector Holders are inserted into the box so that crimp splices can be accommodated. One holder is required for each splice.

**Prysmian Part No. – XCPSC01550 (pack of 50)**



### Pigtails / Adapters

Description	Unit of Supply	SC/UPC	SC/APC
Shuttered Adapter – Simplex	Pack of 10	XPPSC00335	XPPSC00336
Pigtail – green – G657A1 fibre	Pack of 10	XPPSC00341	XPPSC00342

### Patch Chords

For a selection of patchcords please refer to Prysmian data sheet AC004.

## Installation Tools

### Security Screw Driver

The Security Screw Driver is used for installation / re-entering of the Quickdraw Demarcation Unit.

**Prysmian Part No. – XCPSC00669**



Please contact your local sales office listed on [www.prysmiangroup.com](http://www.prysmiangroup.com)

© Prysmian Group 2012, All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.