


RFA 1 5/8" -50 AL Aluminium COAXIAL CABLE
NK CODES
RFA 1 5/8"-50 AL
RFA 1 5/8"-50 AL GHF
RFA 1 5/8"-50 AL BHF
NKRFAL15800
NKRFAL15801
NKRFAL15802
CONSTRUCTION


Inner conductor	Corrugated copper tube	Ø 17.5 mm	(0.69 in)
Dielectric	Cellular polyethylene	Ø 42.0 mm	(1.65 in)
Outer conductor	Corrugated aluminium tube	Ø 46.5 mm	(1.83 in)
Jacket	See Jacketing Options table below	Ø 50.0 mm	(1.97 in)
Marking	Draka, cable type, manufacture week, year, batch number and meter mark		

ELECTRICAL CHARACTERISTICS at +20°C (+68°F)

Characteristic impedance	50 ± 1 Ω
Return loss 24 dB for 100 m cable with NKC connectors	
- 380 - 500	MHz
- 806 - 960	"
- 1710 - 1880	"
- 1900 - 2170	"
Other bands also available on request	
Bands according to customer's specifications	
Attenuation	See table
Velocity factor	0.89
Capacitance	74 pF/m (22.6 pF/ft)
Maximum frequency	2800 MHz
Max power rating	See table
Peak RF voltage rating	5.6 kV
Peak power rating	310 kW
DC-resistance	
- Inner conductor	1.2 Ω/km (0.37 Ω/1000 ft)
- Outer conductor	0.6 Ω/km (0.18 Ω/1000 ft)

MECHANICAL CHARACTERISTICS

Weight	0.87 kg/m (0.58 lb/ft)
Maximum pulling force	2000 N (449 lb)
Minimum bending radius	
- Single bending	200 mm (7.9 in)
- Repeated bending	380 mm (15 in)
Operating temperature range	-55...+80°C (-67...+176 °F)
Crush resistance	1.8 kg/mm (101 lb/in)
Bending moment	49.0 Nm (11.2 lb-ft)
Recommended clamp spacing	1.5 m (4.9 ft)

JACKETING OPTIONS

TYPE	JACKET	IEC 60754 -1/-2 halogen free, non corrosive	IEC 61034 low smoke emission	IEC 60332-3-24 fire retardant	UV retardancy	Min. installation temperature
RFA 1 5/8"-50 AL	Black, halogen free polyethylene (LDPE with HDPE skin)	yes	no	no	yes	-40°C (-40°F)
RFA 1 5/8"-50 AL GHF	Grey, halogen free fire retardant thermoplastic	yes	yes	yes	no	-5°C (23°F)
RFA 1 5/8"-50 AL BHF	Black, halogen free fire retardant thermoplastic	yes	yes	yes	yes	-5°C (23°F)

RFA 1 5/8" -50 AL Aluminium COAXIAL CABLE

FREQUENCY MHz	ATTENUATION dB/100 m	ATTENUATION dB/100 ft	POWER RATING kW
10	0.212	0.065	47
30	0.372	0.113	27
50	0.485	0.148	20.5
88	0.65	0.20	15.3
100	0.70	0.21	14.3
108	0.73	0.22	13.7
174	0.93	0.29	10.6
200	1.01	0.31	9.8
300	1.25	0.38	7.8
400	1.47	0.45	6.7
450	1.56	0.48	6.2
500	1.66	0.51	5.9
512	1.68	0.51	5.8
600	1.84	0.56	5.3
700	2.00	0.61	4.8
800	2.16	0.66	4.5
850	2.23	0.68	4.3
890	2.29	0.70	4.2
900	2.31	0.70	4.2
950	2.38	0.73	4.0
960	2.39	0.73	4.0
1000	2.45	0.75	3.9
1200	2.72	0.83	3.5
1400	2.98	0.91	3.2
1600	3.22	0.98	2.9
1800	3.46	1.05	2.7
1900	3.57	1.09	2.7
2000	3.68	1.12	2.6
2200	3.90	1.19	2.4
2400	4.11	1.25	2.3
2600	4.31	1.31	2.2
2800	4.51	1.37	2.1

Attenuation values are typical at ambient temperature +20°C (+68°F).

Power rating ambient temperature +40°C (+104°F), inner conductor +100°C (+212°F).

CODES FOR NKC CONNECTORS

CONNECTOR TYPE	NK CODE
N male	NKC1158300
N female	NKC1158400
7-16 male	NKC1158100
7-16 female	NKC1158200