

## Internal / External Compact Termination Wall Box

**Prysmian Part Numbers: See Table on page 2**



The Internal / External Compact Termination Wall Box is designed for use in residential, small and large businesses premises. The unit houses a single splice tray and allows fibres from external cables to be spliced to pigtails for connection to customer drop patch cords. The external cable enters from the bottom of the unit, with the customer drop cables (patch cords) exiting from the bottom of the unit or directly through the back of the box and through the wall.

### Features and Benefits

- Termination Box can be mounted internally or externally and is sealed to IP54.
- Removable cover for easy access and fitted with a lock for enhanced security. The unit can be supplied with a keyed lock or a plastic lock which can be turned with a screwdriver.
- Unit manufactured from UV stabilised fire resistant UL94-V0 material allowing external installation.
- Single hinged splice tray enables access for working. The splice tray is supplied interchangeable inserts and can accommodate up to 8 fusion splice protectors of heat shrink or crimp type, or 8 mechanical splices.
- Customer drop cables (patch cords) exit from the bottom of the unit and are sealed using a split grommet. Drop cables can also be routed through the wall.
- Up to 4 SC type pigtails and adapters or 8 LC type pigtails and adapters can be accommodated. A splice only version is also available.
- All fibre are positively bend managed to a 30mm minimum bend radius.
- External input cable enters the unit from the bottom. Cable up to 11mm in diameter can be accommodated .
- For Blown Fibre applications a gas block connector can be housed within the box.
- A knock out is provided in the base of the unit for applications where the customer drop patch cords are required to be routed through the wall into the premises.

### Kit Contents

The External Compact Termination Box is supplied with one splice tray, wall fixings, a cable entry grommet, installation instructions, 8 drop cable grommets, a lock (keyed or screwdriver) and keys and pigtails and adapters where required.

### Additional Items Required

- Splice protectors

### Additional Items Optional

- Gas Seal Connectors

## Technical Data

- Number of Splice Trays: 1
- Maximum Fibre Capacity: 8
- Maximum Input Cable Diameter (mm): 11
- Maximum No. of Input Cables: 1
- IP Rating: 55
- Max Output Cable Diameter (mm): 3.2
- Maximum No. of Output Cables: 8
- Required space envelope (mm): (w) 140 x (h) 185 x (d) 32.
- Operating temperature: -20°C to + 50°C (5 to 95% RH)
- Material:-
  - External Box FR ABS Grey RAL 7030
  - Splice tray: FR ABS Light Grey RAL 7035
- Testing:-
  - Sealing: IP54
  - Dry heat: BS EN 60068-2-2 Test Bb
  - Damp heat: IEC 60068-2-3: 1969
  - Change of temperature: IEC 60068-2-14: 1984
  - Vibration: IEC 60068-2-6: 1995
  - Shock: IEC 60068-2-27: 1987

## Logistics

- Packing Dimensions (mm): (w) 150 x (h) 195 x (d) 40
- Packed Weight (kg): 0.35
- Net weight (kg): 0.30

## Part Numbers

Connector Type	Part Number	
	Keyed Lock	Plastic Lock (Screwdriver entry)
1 x SC/UPC pigtails and adapters	XCPSC00414	XCPSC01197
1 x SC/APC pigtails and adapters	XCPSC00415	XCPSC01198
2 x SC/UPC pigtails and adapters	XCPSC00405	XCPSC01199
2 x SC/APC pigtails and adapters	XCPSC00406	XCPSC01200
4 x SC/UPC pigtails and adapters	XCPSC00407	XCPSC01201
4 x SC/APC pigtails and adapters	XCPSC00408	XCPSC01202
2 x LC/UPC pigtails and adapters	XCPSC00412	XCPSC01203
2 x LC/APC pigtails and adapters	XCPSC00413	XCPSC01204
4 x LC/UPC pigtails and adapters	XCPSC00401	XCPSC01205
4 x LC/APC pigtails and adapters	XCPSC00402	XCPSC01206
8 x LC/UPC pigtails and adapters	XCPSC00403	XCPSC01207
8 x LC/APC pigtails and adapters	XCPSC00404	XCPSC01208
Without pigtails and adapters for SC and LC	XCPSC00409	XCPSC01209
Splice Only Wall Box	XCPSC00920	XCPSC01210

**Note:** The Splice Only Wall Box does not accept SC or LC adapters and pigtails but is for the splicing of drop cables only. Cables are secured to a bracket in the box using cable ties.

## Additional Items Required

### Heat Shrink Splice Protectors

Splice protectors are used to protect the fibre splice. They are 2.4mm in diameter and 45mm in length.


**Prysmian Part No. – XPESC00056 (pack of 12)**  
**XPESC00031 (pack of 50)**



### Crimp Splice Protectors

Crimp Splice Protectors are used to protect the fibre splice. They are 1.3mm wide x 3.2mm high x 30mm long.

**Prysmian Part No. – XKTSC00079 (pack of 12)**  
**XKTSC00078 (pack of 50)**



### Mechanical Splices

Mechanical Splices are used to splice fibres together without the need of a fusion splicing machine. They are 4mm wide x 4mm tall and 40mm in length. An assembly tool and splice holder is required for installation. See Prysmian data sheet AC007 for further information on mechanical splices.

**Prysmian Part No. – XKTSC00121 (pack of 50)**



## Additional Items Optional

### Gas Seal Connector

Used for sealing a Blown Fibre tube. The connector simply push fits over the tube providing a gas tight seal for tubes unpopulated tubes or tubes populated with a Blown Fibre Bundle.

**Prysmian Part No. – XAGSC00404 for 5mm tubes (Pack of 10)**  
**- XBFSC00381 for 7mm tubes (pack of 100)**



Please contact your local sales office listed on [www.prysmiangroup.com](http://www.prysmiangroup.com)

© Prysmian Group 2013, All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.